



Auto-adjustable winding speed corresponds to the label print speed



Noise level below 60dB



Auto-adjustable winding



User-friendly Operation Panel



Up to 6" (inch) Label with Support

# RWG500

Intelligent and Silent Rewinder

# RWG500 - General Specifications

MODEL		BARCODE
Environment	Operating	5 ~ 40°C   30 ~ 80% RH (w/out condensation)
	Storage	-5 ~ 60°C   30 ~ 90% RH (w/out condensation)
Regulatory Approvals		UL/C-UL, FCC, CE, TUV
Dimension (W x D x H) / Weight		280 mm x 320 mm x 230 mm, 7.5k or less
Noise Level		60 dB or less
Power Supply		Optional AC/DC Adapter (Input: AC100/240V): DC+25V, 4A* No need for the following models (CLNX, CLNX Plus, M84Pro)
Printer Connection		Connection cable dedicated for SATO PRINTER: EXT included. Joint plate: Yes** (support following models as standard) [CLNX, CLNX Plus, M84Pro] (Additional kit is required for width over 131 mm) (Additional options are required for width over 131 mm)

WINDING CHARACTERISTICS		
Winding Speed		Automatic speed setting. MAX: 381 mm/sec (15 inch/ sec)
Winding Method		External winding: direct winding on the 38.1 mm spindle (1.5"), or on the 76.2 mm (3") paper core winding
Winding Direction		Face-out/face-in (Counterclockwise / Clockwise)
Winding Monitoring		Automatic control by tension arm position
Winding Outer Diameter		Max winding OD up to 265 mm (11 inch)
Media Size	With, mm	25 · 131 (option 25 - 180)
	Pitch, mm	8 - 400

OPTION		
Rewinder Kit		6-inch expansion kit <with 131 mm - 180 mm>
AC Adapter		AC Adapter

\* SATO Printer EXT Signal Interface: DC +24V, 2A

\*\* Connectivity : EXT Cable Adjustment/Positioning: Joint Plate

## Printer Compatibility



All information in this leaflet is accurate as of 2020 June. Product specifications are subject to change without notice. Any unauthorized reproduction of the contents of this leaflet, in part or whole, is strictly prohibited. All other software, product or company names are trademarks or registered trademarks of their respective owners.



© 2020 SATO CORPORATION. All rights reserved.  
For more information, please contact your local SATO office, or visit: [satoeurope.com](http://satoeurope.com)